



- NOTES:
- 1. SUBSTRATE:
N-BK7
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)



S1 & S2: VIS 0° (425-675nm)
R(avg) ≤0.4% @ 425 - 675nm
 - 3. FINE GROUND SURFACE
 - 4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
 - 5. ROHS COMPLIANT

| |
|--|
| |
| |



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | | |
|-----------------|---------------------|---------------------|---|--------|---|---|-------------------|
| | S1 | S2 | EFL | 100.00 |  Edmund Optics® | | |
| SHAPE | CONVEX | PLANO | BFL | 94.04 | | | |
| RADIUS | 51.68 | ∞ |  | | TITLE | 30mm H x 30mm L x 100mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens | |
| SURFACE QUALITY | 60 - 40 | 60 - 40 | | | | | |
| CLEAR APERTURE | 29.00 x 29.00 | 29.00 x 29.00 | ALL DIMS IN | mm | DWG NO | 25505 | SHEET 15 OF 16 |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED | | | | | |