
Technical Data Sheet

FT-100SHG

F-theta lens for 532nm

Features

- Optimized desing for diffraction limit in all the scanning areas
- Small spot size for microfabrication
- · Compact size and high performance
- precise marking / etching / melting



Specifications

Focal length	101.9 mm	
Designed wavelength	532 nm	
Scanning area	56.5×56.5 mm ²	
Max. input beam diameter	φ12.0 mm	
1/e ² beam spot size	φ8 . 5 μm	
Working distance	94.5 mm	

Mirror distance	1st mirror-2nd mirror	18mm
(recommend)	2nd mirror-housing	13.5mm
Mount screw	M85×1	
scan angle	±22.68 degrees	
Total transmission	T ≧ 95%	
Material	Optical glass	

Outline

