NOTES:

1. SUBSTRATE: SAPPHIRE (AL2O3) DO NOT MANUFACTURE PARTS TO THIS DRAWING


- 2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤ 3.5 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)


S1 & S2: R(ABS) ≤1.5% @ 750 - 800nm R(ABS) ≤1.0% @ 800 - 1550nm R(AVG)avg ≤0.7% @ 750 - 1550nm



FINE GRIND SURFACE

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | \$1 | \$2 |
|---|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| CLEAR APERTURE | Ø18.00 | Ø18.00 |
| SURFACE FLATNESS | 2λ | 2λ |
| SURFACE QUALITY | 80-50 | 80-50 |
| BIREFRINGENCE (n _o -n _e) | 0.008 | 0.008 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

| | | | Edmund Optics® | | | |
|---|------------------------|-------------|-----------------------|--|---|--|
| | THIRD ANGLE PROJECTION | $\phi \lhd$ | TITLE | 20mm Dia., 1mm Thick, NIR II AR Coa Sapphire Window | 20mm Dia., 1mm Thick, NIR II AR Coated Sapphire Window | |
|) | ALL DIMS IN | mm | DWG NO | 20945 | SHEET 1 OF 1 | |