

Reflektierender Neutrale Dichtefilter mit OD 0,1; 25,4 mm Durchm.



Produkt #27-926 **AUSVERKAUF** **4 In Stock**

€15⁹⁵

+ WARENKORB

Mengenrabatte	
Stk. 1+	€15,95 stückpreis
Need More?	Angebotsanfrage

i Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails

Neutral Density Filter **Typ:**

Physikalische und mechanische Eigenschaften

25.40 ±0.3 **Durchmesser (mm):**

1.00 ±0.25 **Dicke (mm):**

±3 **Parallelität (Bogenminuten):**

±0.3 Toleranz Größe (mm):

>90 Freie Apertur (%):

Optische Eigenschaften

0.1 Optische Dichte OD:

Borosilicate Substrat:

Metallic Based ND Beschichtung:

79.00 Transmission (%):

±10 Toleranz optische Dichte (%):

Konformität mit Standards

[Anzeigen](#) Konformitätszertifikat:

Produktdetails

- Feature Standard Designs and Specifications
- Constant Density Values Across the Surface
- For More Options, View Precision Quality [Reflective Neutral Density Filters](#)

Neutral density filters have constant density values across the surface. In stacks, the total density is the sum of each filter's density. Neutral density filters are primarily used for the attenuation of light over a wide spectral range. They are often used in laser and photometer applications, where excessive power can cause damage or inaccurate results. Commercial Grade Reflective Neutral Density Filters offer commercial quality, at an affordable price.

Note: Orient the mirrored side toward the source at an angle of incidence of 0°.