


NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: YAG-BBAR (500-1100nm)  
S2: YAG-BBAR (500-1100nm)  
Rabs <0.25% @ 532nm   Rabs <0.25% @ 1064nm   Ravg <1.0% @ 500 - 1100nm

4. FINE GRIND SURFACE

- 5. ROHS COMPLIANT
- 6. TRANSMITTED WAVEFRONT (P-V):  
λ/4 (per inch over clear aperture)




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø 18.00	Ø 18.00
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE  
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

20mm Dia., 2mm Thick, YAG-BBAR Coated  
λ/4 N-BK7 Window

DWG NO

23472

SHEET  
78 OF 84