




NOTES:

1. SUBSTRATE:
H-K9L
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: MgF₂ (400-700nm)
R(AVG) ≤ 1.75% @ 400 - 700nm
3. CENTERING: ≤30 ARCMIN



FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	8.30	 Edmund Optics ®		
SHAPE	CONVEX	CONVEX	BFL @ 587.6nm	5.58			
SURFACE QUALITY	80-50 (typical)	80-50 (typical)			TITLE	16mm Dia. x 8.3mm FL, MgF2 Coated, PCX Condenser Lens	
CLEAR APERTURE	Ø 14.40	Ø 14.40			DWG NO	23813	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm			