

NOTES:
1. SUBSTRATE:
FUSED SILICA


2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Ravg ≥78% @ 120 - 125nm
Ravg ≥85% @ 120 - 600nm
S2: COMMERICAL POLISH

3. FINE GRIND SURFACE



4. FOCAL LENGTH TOLERANCE:

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	CONCAVE	PLANO				
SURFACE QUALITY	20-10	N/A				
COATING TYPE	METAL	N/A				
COATING	Enhanced Aluminum (120-600nm)	N/A	TITLE 25.4mm Dia., 25mm FL, Vacuum UV (VUV) Spherical Mirror			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				
ALL DIMS IN			mm	DWG NO	24056	SHEET 1 OF 1