


NOTES:

- 1. SUBSTRATE: Fused Silica (Corning 7980)
- 2. RoHS COMPLIANT
- 3. SURFACE S2 TO BE PARALLEL WITH SURFACE S 1 TO WITHIN ACRMINS
- 4. Coating (Apply Across Clear Aperture):
 - S1 & S2: Rabs ≤1.0% @ 250 - 425nm
 - Ravg ≤0.75% @ 250 - 425nm
 - Ravg ≤0.5% @ 370 - 420nm

5. FINE GROUND SURFACE




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
Shape	Plano	Plano
Surface Accuracy	1λ	1λ
Surface Quality	60-40	60-40
Clear Aperture	45.72	45.72
Bevel	Protected as Needed	Protected as Needed

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

50.8mm Dia. 2mm Thick UV-AR Coated, 1λ
Fused Silica Window

DWG NO

25259

SHEET
16 OF 101