



FOCAL LENGTH (EFL):  $40 \pm 0,4$   
 BACK FOCAL LENGTH (BFL):  $37,2$

1 785nm V-COAT  
 R(ABS) < 0,25% @ 785nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 31,39 CX Øe 29 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -	GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 29 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,27' 5/ 40 - 20 6/ -

PROTECTIVE CHAMFERS AS NEEDED		FIRST ANGLE PROJECTION	 <b>Edmund Optics®</b>	
ROHS: COMPLIANT	SCALE: NONE			
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY. DO NOT MANUFACTURE PARTS TO THIS DRAWING			TITLE	30mm Dia x 40mm FL, 785nm V-Coat Coated, Plano-Convex Lens
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN: mm	DWG NO
			SHEET T SIZE	A4
			SHEET	1 OF 1