





FOCAL LENGTH (EFL): $-12 \pm 0,12$
 BACK FOCAL LENGTH (BFL): $-12,99$

- 1 VIS-EXT
 $R(AVG) \leq 0,5\%$ FROM 350 - 700nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 6,2 CV Øe 5,4 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 5,4 (λ) SEE NOTE 1 3/ 3 (0,5) λ=632,8 nm 4/ 1,93' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 6mm Dia x -12mm FL, VIS-EXT Coated, Plano-Concave Lens DWG NO 26656 SHEET SIZE A4 SHEET 1 OF 1	