





f' : $-12 \pm 0,12$

BACK FOCAL LENGTH (BFL): $-13,38$



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 5,5 CV			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL		
Øe 5,4				Øe 5,4		
λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00%				λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00%		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ 2,18'				4/ -		
5/ 40 - 20				5/ 40 - 20		
6/ -			6/ -			
						
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	6mm Dia x -12mm FL, UV-VIS Coated, Plano-Concave Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO	71092
			SHEET SIZE A4			
			SHEET 1 OF 1			