





f' : $-50 \pm 0,5$

BACK FOCAL LENGTH (BFL): $-51,37$



LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R 22,923 CV			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL		
Øe 11				Øe 11		
λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00%				λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00%		
3/ 3 (0,5) λ=632,8 nm				3/ 3 (0,5) λ=632,8 nm		
4/ 2,18'				4/ -		
5/ 40 - 20				5/ 40 - 20		
6/ -				6/ -		
P				P		
PROTECTIVE CHAMFERS AS NEEDED			EO ® Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			TITLE 12mm Dia x -50mm FL, UV-VIS Coated, Plano-Concave Lens			
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING						
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO 71100			
			SHEET SIZE A4			
			SHEET 1 OF 1			