

[Alle Produkte](#) / [Optikkomponenten](#) / [Optische Linsen](#) / [Achromate](#)

TECHSPEC® Achromatische Fokussierduplets mit Luftspalt für Nd:YAG



- Farbkorrigiert bei 632,8 nm und 1064 nm
- Optimiert für geringe sphärische Aberration
- Minimale Spotgröße für Werkstoffbearbeitung

Spezifikationen


Physikalische und mechanische Eigenschaften

Freie Apertur CA (mm):	27.0	Luftspalt (mm):	1.0
Aufbau:	Anodized Aluminum Housing		

Optische Eigenschaften

Substrat:	N-SK5 / N-SF57		
Oberflächenqualität:	20-10	Beschichtung:	Dual V-Coat (632.8 and 1064nm)
Beschichtungsspezifikation:	R _{abs} <0.5% @ 1030 - 1090nm R _{abs} <1.0% @ 632.8nm	Designwellenlänge DWL (nm):	632.8, 1064
Transmittierter Wellenfrontfehler, RMS:	λ/4 On central 18mm		

Technische Informationen



Produkte

EFL (mm)	Substrat	Beschichtung	Gehäusedurchmesser (mm)	Aufbau	Transmittierter Wellenfrontfehler, RMS	Artikelnummer	Preis	Kaufen
80.00	N-SK5 / N-SF57	Dual V-Coat (632.8 and 1064nm)	36	Anodized Aluminum Housing	$\lambda/4$ On central 18mm	#12-163	€705,00 Mengenrabatte	1 In Stock
100.00	N-SK5 / N-SF57	Dual V-Coat (632.8 and 1064nm)	36	Anodized Aluminum Housing	$\lambda/4$ On central 18mm	#12-160	€705,00 Mengenrabatte	Kontakt
150.00	N-SK5 / N-SF57	Dual V-Coat (632.8 and 1064nm)	36	Anodized Aluminum Housing	$\lambda/4$ On central 18mm	#12-159	€705,00 Mengenrabatte	2 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Telefonnr.: 1-800-363-1992 :
www.edmundoptics.com