

**TECHSPEC® Plankonvexe Linse, 12 mm D. x 48 mm BW, NIR-I-beschichtet**



Produkt **#48-739** **20+ In Stock**

[Andere Beschichtungen](#)

1  €47<sup>90</sup>

**+ WARENKORB**

Mengenrabatte

|            |                                 |
|------------|---------------------------------|
| Stk. 1-9   | €47,50 stückpreis               |
| Stk. 10-24 | €42,50 stückpreis               |
| Stk. 25-49 | €38,00 stückpreis               |
| Need More? | <a href="#">Angebotsanfrage</a> |

! Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

**Produktdetails**

Plano-Convex Lens

Typ:

**Physikalische und mechanische Eigenschaften**

|                      |                                    |
|----------------------|------------------------------------|
| 12.00 +0.0/-0.025    | <b>Durchmesser (mm):</b>           |
| <1                   | <b>Zentrierung (Bogenminuten):</b> |
| 2.50 ±0.05           | <b>Mittendicke CT (mm):</b>        |
| 1.76                 | <b>Randdicke ET (mm):</b>          |
| 11                   | <b>Freie Apertur CA (mm):</b>      |
| Protective as needed | <b>Fase:</b>                       |

## Optische Eigenschaften

|  |   |
|--|---|
| 48.00 @ 587.6nm                        | <b>Effektive Brennweite EFL (mm):</b>                         |
| 46.36                                  | <b>Hintere Brennweite BFL (mm):</b>                           |
| NIR I (600-1050nm)                     | <b>Beschichtung:</b>  |
| R <sub>avg</sub> ≤ 0.5% @ 600 - 1050nm | <b>Beschichtungsspezifikation:</b>                            |
| <b>N-BK7</b>                           | <b>Substrat:</b> <input type="checkbox"/>                     |
| 40-20                                  | <b>Oberflächenqualität:</b>                                   |
| 1.5λ                                   | <b>Power (P-V) @ 632,8 nm:</b>                                |
| λ/4                                    | <b>Unregelmäßigkeit (P-V) @ 632,8 nm:</b>                     |
| ±1                                     | <b>Toleranz Brennweite (%):</b>                               |
| 24.82                                  | <b>Radius R<sub>1</sub> (mm):</b>                             |
| 4                                      | <b>Blende:</b>  |
| 0.13                                   | <b>Numerische Apertur NA:</b>                                 |
| 600 - 1050                             | <b>Wellenlängenbereich (nm):</b>                              |
| 7 J/cm <sup>2</sup> @ 1064nm, 10ns     | <b>Zerstörschwelle, laut Design:</b> <input type="checkbox"/> |

## Konformität mit Standards

|                 |                                |
|-----------------|--------------------------------|
| <b>Konform</b>  | <b>RoHS 2015:</b>              |
| <b>Konform</b>  | <b>Reach 219:</b>              |
| <b>Anzeigen</b> | <b>Konformitätszertifikat:</b> |

## Gewünschte Spezifikationen nicht dabei?

Edmund Optics bietet einen umfangreichen kundenspezifischen Fertigungsservice für Optik- und Bildverarbeitungs-komponenten an, speziell hergestellt für Ihre Anwendungsanforderungen. Wir ermöglichen flexible Lösungen für Ihre Bedürfnisse – von der Prototypenphase bis zur Serienfertigung. Unsere erfahrenen IngenieurInnen freuen sich auf die Zusammenarbeit und unterstützen Sie bei jedem Projektschritt.

Unser Service beinhaltet:

- Kundenspezifische Abmessungen, Materialien und mehr
- Hochpräzise Oberflächenqualität und -ebenheit
- Enge Toleranzen und komplexe Formen
- Skalierbare Produktion – vom Prototypen zur Serie

Erfahren Sie mehr über unsere [kundenspezifischen Fertigungsmöglichkeiten](#) oder senden Sie [hier](#) eine Anfrage.

## Produktdetails

- AR-beschichtet für <0,5% Reflexion pro Oberfläche bei 600 - 1050 nm
  - Entwickelt für einen Einfallswinkel von 0°
  - Verschiedene Antireflexionsbeschichtungen erhältlich: **MgF<sub>2</sub>**, **VIS 0°**, **VIS-NIR**, **NIR II**, **VIS-EXT** und **YAG-BBAR** oder **unbeschichtet**
- TECHSPEC® Plankonvexe Linsen (PCX) mit NIR-I-Beschichtung haben eine positive Brennweite und sind ideal für die Fokussierung von Licht in abbildenden Anwendungen. Sie können gut in Verbindung mit Emittoren, Detektoren, Lasern und Faseroptiken eingesetzt werden. TECHSPEC® Plankonvexe Linsen (PCX) mit NIR-I-Beschichtung sind in einer Vielzahl von Durchmessern und Brennweiten erhältlich. Identische Designs dieser Linsen werden auch **unbeschichtet** oder mit breitbandigen Antireflexionsbeschichtungen (BBAR) angeboten, dazu gehören **MgF<sub>2</sub>**, **VIS 0°**, **VIS-NIR**, **NIR II**, **VIS-EXT** und **YAG-BBAR**.

## Technische Informationen



N-BK7

### Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

### N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% @ 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$\begin{aligned} R_{abs} &\leq 0.25\% @ 880\text{nm} \\ R_{avg} &\leq 1.25\% @ 400 - 870\text{nm} \\ R_{avg} &\leq 1.25\% @ 890 - 1000\text{nm} \end{aligned}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



[Click Here to Download Data](#)

**N-BK7 with VIS 0° Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

**N-BK7 with YAG-BBAR Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 0.25\% @ 532\text{nm}$$

$$R_{abs} \leq 0.25\% @ 1064\text{nm}$$

$$R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

**N-BK7 with NIR I Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

**N-BK7 with NIR II Coating  
Typical Transmission**



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$$

$$R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$$

$$R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## Kompatible Halterungen

---