

TECHSPEC® Plankonvexe Linse, 20 mm D. x 70 mm BW, VIS-EXT-beschichtet



Produkt **#88-716**

KONTAKT

▢ [Andere Beschichtungen](#)

-

1

+

€51<sup>,00</sup>

+ WARENKORB

| Mengenrabatte |                                 |
|---------------|---------------------------------|
| Stk. 1-9      | €51,00 stückpreis               |
| Stk. 10-24    | €45,75 stückpreis               |
| Stk. 25-49    | €40,75 stückpreis               |
| Need More?    | <a href="#">Angebotsanfrage</a> |

!

 Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails

Plano-Convex Lens

Typ:

Physikalische und mechanische Eigenschaften

|                      |                             |
|----------------------|-----------------------------|
| 20.00 +0.0/-0.025    | Durchmesser (mm):           |
| <1                   | Zentrierung (Bogenminuten): |
| 3.00 ±0.10           | Mittendicke CT (mm):        |
| 1.59                 | Randdicke ET (mm):          |
| 19                   | Freie Apertur CA (mm):      |
| Protective as needed | Fase:                       |

|                                   |                                    |
|-----------------------------------|------------------------------------|
| Optische Eigenschaften            |                                    |
| 70.00 @ 587.6nm                   | Effektive Brennweite EFL (mm):     |
| 68.03                             | Hintere Brennweite BFL (mm):       |
| VIS-EXT (350-700nm)               | Beschichtung:                      |
| Ravg <0.5% @ 350 - 700nm          | Beschichtungsspezifikation:        |
| N-BK7                             | Substrat: □                        |
| 40-20                             | Oberflächenqualität:               |
| 1.5λ                              | Power (P-V) @ 632,8 nm:            |
| λ/4                               | Unregelmäßigkeit (P-V) @ 632,8 nm: |
| ±1                                | Toleranz Brennweite (%):           |
| 36.18                             | Radius R <sub>1</sub> (mm):        |
| 3.5                               | Blende:                            |
| 0.14                              | Numerische Apertur NA:             |
| 350 - 700                         | Wellenlängenbereich (nm):          |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns | Zerstörschwelle, laut Design: □    |

|                           |                         |
|---------------------------|-------------------------|
| Konformität mit Standards |                         |
| Konform                   | RoHS 2015:              |
| Anzeigen                  | Konformitätszertifikat: |
| Konform                   | Reach 235:              |

## Gewünschte Spezifikationen nicht dabei?

Edmund Optics bietet einen umfangreichen kundenspezifischen Fertigungsservice für Optik- und Bildverarbeitungskomponenten an, speziell hergestellt für Ihre Anwendungsanforderungen. Wir ermöglichen flexible Lösungen für Ihre Bedürfnisse – von der Prototypenphase bis zur Serienfertigung. Unsere erfahrenen IngenieurInnen freuen sich auf die Zusammenarbeit und unterstützen Sie bei jedem Projektschritt.

Unser Service beinhaltet:

- Kundenspezifische Abmessungen, Materialien und mehr
- Hochpräzise Oberflächenqualität und -ebenheit
- Enge Toleranzen und komplexe Formen
- Skalierbare Produktion – vom Prototypen zur Serie

Erfahren Sie mehr über unsere [kundenspezifischen Fertigungsmöglichkeiten](#) oder senden Sie [hier](#) eine Anfrage.

## Produktdetails

- Breitband-Antireflexbeschichtung für das sichtbare Spektrum mit verbesserten UV-Eigenschaften
- Reflexion pro Oberfläche <0,5% im Bereich von 350 – 700 nm
- Für 0° Einfallswinkel ausgelegt
- Verschiedene Beschichtungen erhältlich: [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#) und [YAG-BBAR](#) oder [unbeschichtet](#)


TECHSPEC® Plankonvexe Linsen (PCX) mit VIS-EXT-Beschichtung haben eine positive Brennweite und sind ideal für die Fokussierung von Licht in abbildenden Anwendungen. Sie können gut in Verbindung mit Emittern, Detektoren, Lasern und Faseroptiken eingesetzt werden. TECHSPEC® Plankonvexe Linsen (PCX) mit VIS-EXT-Beschichtung sind in einer Vielzahl von Durchmessern und Brennweiten erhältlich. Identische Designs dieser Linsen werden auch [unbeschichtet](#) oder mit breitbandigen Antireflexionsbeschichtungen (BBAR) angeboten, dazu gehören [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#) und [YAG-BBAR](#).

Technische Informationen



N-BK7


Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.

[Click Here to Download Data](#)

N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with VIS-NIR Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$\begin{aligned} R_{abs} &\leq 0.25\% \text{ @ } 880\text{nm} \\ R_{avg} &\leq 1.25\% \text{ @ } 400 - 870\text{nm} \\ R_{avg} &\leq 1.25\% \text{ @ } 890 - 1000\text{nm} \end{aligned}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

|                                                                                                                                                                                                                                                                                                                                                                               |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>2004006008001000120014001600</div> <div>Wavelength (nm)</div>                                                                                                                                                                                                                                                                                                            |  |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| <div><div>N-BK7 with VIS 0° Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div></div></div></div>                                                             |  | <div>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                        |
| <div><div>N-BK7 with YAG-BBAR Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div></div></div></div>                             |  | <div>Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math><br/><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>           |
| <div><div>N-BK7 with NIR I Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div></div></div></div>                                |  | <div>Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}</math></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div>                                                                                                                     |
| <div><div>N-BK7 with NIR II Coating</div><div>Typical Transmission</div><div><div><div>T (%)</div><div>100</div><div>95</div><div>90</div><div>85</div><div>80</div><div>75</div><div>70</div></div><div><div>200</div><div>400</div><div>600</div><div>800</div><div>1000</div><div>1200</div><div>1400</div><div>1600</div><div>1800</div><div>2000</div></div></div></div> |  | <div>Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</div> <div>The blue shaded region indicates the coating design wavelength range, with the following specification:</div> <div><div><math>R_{abs} \leq 1.5\% @ 750 - 800\text{nm}</math><br/><math>R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}</math><br/><math>R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}</math></div></div> <div>Data outside this range is not guaranteed and is for reference only.</div> <div><a href="#">Click Here to Download Data</a></div> |

