

Strichplatte, 20,0 mm Durchmesser, 10 mm / 100 Einteilungen



Produkt **#68-790**

KONTAKT

-

1

+

€198^{,00}

+ WARENKORB

Mengenrabatte	
Stk. 1-4	€198,00 stückpreis
Stk. 5-9	€188,00 stückpreis
Need More?	Angebotsanfrage

!

 Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Konformität mit Standards

Anzeigen

Konformitätszertifikat:

Produktdetails

- Vergrößerungen von 2,4X - 320X

- Ergonomisches Design vereinfacht die Nutzung
 - Modulares Design für kundenspezifische Anforderungen
- Diese Z Serie modularer Zoom Stereomikroskope ist die perfekte Wahl für den Aufbau eines neuen Inspektionssystems mit einfach verwendbaren Komponenten. Mit 3 Zoombereichen und mehreren Objektiven und Okularen lassen sich diese Systeme einfach kundenspezifisch anpassen, um Ihre spezifischen Anforderungen zu erfüllen. Optionale Komponenten sind u. a. ein Tubus mit Strahlteiler, ein C-Mbunt Adapter an den eine Kamera angeschlossen werden kann, sowie [LED Ringlichter](#) mit Intensitätssteuerung.

Technische Informationen

Description				Stock No.
Main Body	One Required	0.8X - 8.0X Zoom Body Z Series Microscope, Z10		#68-772
		0.8X - 6.4X Zoom Body Z Series Microscope, Z8		#68-773
		0.8X - 5.0X Zoom Body Z Series Microscope, Z6		#68-774
Viewing Head	One Required	Binocular Mcroscope Head 20° Incline		#68-775
		Ergonomic Microscope Head 0-35° Incline		#68-776
Eyepieces	Two Required	WF 10XEyepiece with 24mm FOV, Compatible w/ 26.5mm Reticle		#68-777
		WF 15XEyepiece with 16mm FOV, Compatible w/ 20.0mm Reticle		#68-778
		WF 20XEyepiece with 12.5mm FOV, Not Reticle Compatible		#68-779
Objective	One Required	0.3XAchromatic Z Series Objective, 0.03 NA, 280mm WD		#68-780
		0.5XPlan Apochromatic Z Series Objetive, 0.05 NA, 126mm WD		#68-781
		1.0XPlan Apochromatic Z Series Objective, 0.09 NA, 78mm WD		#68-782
		2.0XPlan Apochromatic Z Series Objective, 0.02 NA, 32.5mm WD		#68-783
Riser Objective	One Required, if using 0.3X or 0.5X Objective	Rise Adapter		#88-609
Stand	One Required	Standard Microscope Stand with 76mm Holder		#68-784
		Variable LED Mcroscope Stand with 76mm Holder		#68-785

Objective	Working Distance (mm)	10XEyepieces					
		Z10 (0.8X - 8.0X)		Z8 (0.8X - 6.4X)		Z6 (0.8X - 5.0X)	
		Magnification	FOV (mm)	Magnification	FOV (mm)	Magnification	FOV (mm)
0.3X	280	2.4X - 24X	100 - 10	2.4X - 19.5X	100 - 12.3	2.4X - 15X	100 - 16
0.5X	126	4X - 40X	60 - 6	4X - 32.5X	60 - 70.4	4X - 25X	60 - 9.6
1.0X	78	8X - 80X	30 - 3	8X - 65X	30 - 3.7	8X - 50X	30 - 4.8
2.0X	32.5	16X - 160X	15 - 1.5	16X - 130X	15 - 1.85	16X - 100X	15 - 2.4
Objective	Working Distance (mm)	15XEyepieces					
		Z10 (0.8X - 8.0X)		Z8 (0.8X - 6.4X)		Z6 (0.8X - 5.0X)	
		Magnification	FOV (mm)	Magnification	FOV (mm)	Magnification	FOV (mm)
0.3X	280	3.6X - 36X	66.7 - 6.67	3.6X - 29.3X	66.7 - 8.2	3.6X - 22.5X	66.7 - 10.67
0.5X	126	6X - 60X	40 - 4	6X - 52X	40 - 4.9	6X - 37.5X	40 - 6.4
1.0X	78	12X - 120X	20 - 2	12X - 97.5X	20 - 2.5	12X - 75X	20 - 3.2
2.0X	32.5	24X - 240X	10 - 1	24X - 195X	10 - 1.23	24X - 150X	10 - 1.6
Objective	Working Distance (mm)	20XEyepieces					
		Z10 (0.8X - 8.0X)		Z8 (0.8X - 6.4X)		Z6 (0.8X - 5.0X)	
		Magnification	FOV (mm)	Magnification	FOV (mm)	Magnification	FOV (mm)
0.3X	280	4.8X - 48X	50 - 5	4.8X - 39X	50 - 6.15	4.8X - 30X	50 - 8
0.5X	126	8X - 80X	30 - 3	8X - 65X	30 - 3.7	8X - 50X	30 - 4.8
1.0X	78	16X - 160X	15 - 1.5	16X - 130X	15 - 1.85	16X - 100X	15 - 2.4
2.0X	32.5	32X - 320X	7.5 - 0.75	32X - 260X	7.5 - 0.9	32X - 200X	7.5 - 1.2