

TECHSPEC<sup>®</sup> Plankonvexe Linse aus UV-Quarzglas, 20 mm D. x 60 mm BW, NIR-I-beschichtet



UV Fused Silica Plano-Convex (PCX) Lenses



Produkt #18-170 12 In Stock

-

1

+

€168<sup>.00</sup>

+ WARENKORB

| Mengenrabatte |                                 |
|---------------|---------------------------------|
| Stk. 1-5      | €168,00 stückpreis              |
| Stk. 6-25     | €134,00 stückpreis              |
| Stk. 26-49    | €126,00 stückpreis              |
| Need More?    | <a href="#">Angebotsanfrage</a> |

ⓘ Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails

Plano-Convex Lens

Typ:

Physikalische und mechanische Eigenschaften

|                      |                             |
|----------------------|-----------------------------|
| 20.00 -0.025         | Durchmesser (mm):           |
| <1                   | Zentrierung (Bogenminuten): |
| 3.50 ±0.10           | Mittendicke CT (mm):        |
| 1.62                 | Randdicke ET (mm):          |
| 19                   | Freie Apertur CA (mm):      |
| Protective as needed | Fase:                       |

|                                       |                                    |
|---------------------------------------|------------------------------------|
| Optische Eigenschaften                |                                    |
| 60.00 @ 587.6nm                       | Effektive Brennweite EFL (mm):     |
| 57.60                                 | Hintere Brennweite BFL (mm):       |
| NIR I (600-1050nm)                    | Beschichtung:                      |
| R <sub>avg</sub> ≤0.5% @ 600 - 1050nm | Beschichtungsspezifikation:        |
| Fused Silica (Corning 7980)           | Substrat: □                        |
| 40-20                                 | Oberflächenqualität:               |
| 3 Rings                               | Power (P-V) @ 632,8 nm:            |
| 0.5 Rings                             | Unregelmäßigkeit (P-V) @ 632,8 nm: |
| ±1                                    | Toleranz Brennweite (%):           |
| 27.51                                 | Radius R <sub>1</sub> (mm):        |
| 3                                     | Blende:                            |
| 0.17                                  | Numerische Apertur NA:             |
| 600 - 1050                            | Wellenlängenbereich (nm):          |
| 7 J/cm <sup>2</sup> @ 1064nm, 10ns    | Zerstörschwelle, Referenz: □       |

|                           |                         |
|---------------------------|-------------------------|
| Konformität mit Standards |                         |
| Konform                   | RoHS 2015:              |
| Anzeigen                  | Konformitätszertifikat: |
| Konform                   | Reach 235:              |

## Gewünschte Spezifikationen nicht dabei?

Edmund Optics bietet einen umfangreichen kundenspezifischen Fertigungsservice für Optik- und Bildverarbeitungskomponenten an, speziell hergestellt für Ihre Anwendungsanforderungen. Wir ermöglichen flexible Lösungen für Ihre Bedürfnisse – von der Prototypenphase bis zur Serienfertigung. Unsere erfahrenen IngenieurInnen freuen sich auf die Zusammenarbeit und unterstützen Sie bei jedem Projektschritt.

Unser Service beinhaltet:

- Kundenspezifische Abmessungen, Materialien und mehr
- Hochpräzise Oberflächenqualität und -ebenheit
- Enge Toleranzen und komplexe Formen
- Skalierbare Produktion – vom Prototypen zur Serie

Erfahren Sie mehr über unsere [kundenspezifischen Fertigungsmöglichkeiten](#) oder senden Sie [hier](#) eine Anfrage.

## Produktdetails

- AR-Beschichtung bietet <0,5% Reflexion pro Oberfläche für 600-1050 nm
- Präzise Quarzglassubstrate
- Verschiedene Beschichtungen verfügbar: [Unbeschichtet](#), [MgF<sub>2</sub>](#), [UV-AR](#), [UV-VIS](#), [VIS-NIR](#), [VIS 0°](#), [YAG-BBAR](#), [NIR II](#) und [VIS-EXT](#)

TECHSPEC® Plankonvexe Linsen (PCX) aus UV-Quarzglas zeichnen sich durch Präzisionsspezifikationen und eine Vielzahl von Beschichtungsmöglichkeiten auf einem breitbandigen Substrat aus. Quarzglas wird üblicherweise in Anwendungen von Ultraviolett (UV) bis Nahinfrarot (NIR) verwendet. Aufgrund seines niedrigen Brechungsindex, seines niedrigen Wärmeausdehnungskoeffizienten und seiner geringen Einschlüsse ist es ideal für Laseranwendungen und raue Umgebungsbedingungen. TECHSPEC Plankonvexe Linsen (PCX) aus UV-Quarzglas mit branchenweit führenden Spezifikationen für Durchmesser und Zentrierung eignen sich ideal für die Integration in anspruchsvolle Bildgebungs- und Messanwendungen.

Technische Informationen

FUSED SILICA


Uncoated Fused Silica  
Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

Fused Silica with MgF<sub>2</sub> Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-AR Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$   
 $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$   
 $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Fused Silica with UV-VIS Coating  
Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.



The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.0\% @ 350 - 450\text{nm}$   
 $R_{avg} \leq 1.5\% @ 250 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

|                                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| <p data-bbox="569 252 1079 359"><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>       | <p data-bbox="1341 436 1839 486">Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p data-bbox="1331 498 1850 549">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 560 1703 587"><math>R_{avg} \leq 0.5\% @ 350 - 700\text{nm}</math></p> <p data-bbox="1341 599 1839 649">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1472 661 1709 685"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                  |
| <p data-bbox="573 928 1075 1035"><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>    | <p data-bbox="1341 1077 1839 1127">Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p data-bbox="1331 1139 1850 1190">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1493 1202 1688 1228"><math>R_{abs} \leq 0.25\% @ 880\text{nm}</math></p> <p data-bbox="1472 1228 1709 1255"><math>R_{avg} \leq 1.25\% @ 400 - 870\text{nm}</math></p> <p data-bbox="1465 1255 1715 1282"><math>R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}</math></p> <p data-bbox="1341 1308 1839 1359">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1472 1371 1709 1394"><a href="#">Click Here to Download Data</a></p> |
| <p data-bbox="569 1602 1079 1709"><b>Fused Silica with VIS 0° Coating</b><br/><b>Typical Transmission</b></p>    | <p data-bbox="1331 1780 1850 1831">Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.</p> <p data-bbox="1331 1843 1850 1893">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1478 1905 1703 1932"><math>R_{avg} \leq 0.4\% @ 425 - 675\text{nm}</math></p> <p data-bbox="1341 1944 1839 1994">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1472 2006 1709 2030"><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                         |
| <p data-bbox="548 2273 1100 2380"><b>Fused Silica with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1341 2427 1839 2478">Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p data-bbox="1331 2490 1850 2540">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p data-bbox="1493 2552 1688 2579"><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math></p> <p data-bbox="1493 2579 1688 2605"><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math></p> <p data-bbox="1472 2605 1709 2632"><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p data-bbox="1341 2644 1839 2694">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1472 2706 1709 2730"><a href="#">Click Here to Download Data</a></p>      |

|                                                                                                                                                                                                |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div data-bbox="260 121 1291 753"><h3>Fused Silica with NIR I Coating<br/>Typical Transmission</h3></div>    | <div data-bbox="1325 299 1858 552"><p>Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.5\%</math> @ 600 - 1050nm</p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                        |
| <div data-bbox="260 804 1291 1406"><h3>Fused Silica with NIR II Coating<br/>Typical Transmission</h3></div> | <div data-bbox="1325 940 1858 1264"><p>Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 1.5\%</math> @ 750 - 800nm<br/><math>R_{abs} \leq 1.0\%</math> @ 800 - 1550nm<br/><math>R_{avg} \leq 0.7\%</math> @ 750 - 1550nm</p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |