

Wählen Sie bitte das Land, in das geliefert werden soll, um genauere Informationen zur Verfügbarkeit zu erhalten:

Wählen Sie Ihr Land/Ihre Region:

European Union▼

SUBMIT



2.5mm CA, VIS Coated, 70 Diopter Focus Range, Corning® Varioptic® Variable Focus Liquid Lens Development Kit



Produkt #19-357

AUSVERKAUF

3-4 TAGE

-

 1

+

€601,95

+ WARENKORB

Stk. 1+

€601,95

Mengenrabatte

[Angebotsanfrage](#)

🔔

 Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich



Durchmesser (mm):
9.40 (packaged lens, 7.75 bare lens)

Beschichtung:
VIS

Typ: Development Kit
Freie Apertur CA (mm): 2.5
Inhalt des Sets: Corning® Varioptic® A-25H0-D0 Lens (without cable) A-25H0-D0-P07 Lens (with straight flex cable : 4 pins) Maxim MAX14574 Driver Board (with 4 pin connector and 6 pin connector for thermistor populated 6 pin FPC) USB-MFlexiboard (with 4 and 6 pin connector and USB compatibility) M4 thread holder for lens Bent Flex Cable FPC-A-03 Control Software Documentation Package
Fokusbereich: -35 to +35 diopter
Modellnummer: D-A-25H0-D0
Betriebstemperatur (°C): -20 to +60
Lagerungstemperatur (°C): -40 to +85
Dicke (mm): 3.50 (packaged lens, 2.15 bare lens)
Transmission (%): 96 @ 587nm
Transmittierter Wellenfrontfehler, RMS: 70nm
Typische Anwendungen: Very close auto-focus or continuous auto-focus applications in portable devices and in laser or lighting applications for variable focus and expansion control. Features 3X higher dynamic range over the A- 25HX lens.

Konformität mit Standards

RoHS 2015: Konform
Reach 224: Konform
Konformitätszertifikat: Anzeigen