

TECHSPEC®Keilfenster aus N-BK7, 25 mm Durchmesser

Mehr Produkte vonSCHOTT Optical Components



Produkt #34-245 2 In Stock

-

1

+

€127⁷²

+ WARENKORB

Mengenrabatte	
Stk. 1-5	€127,72 stückpreis
Stk. 6-25	€101,97 stückpreis
Stk. 26-49	€95,79 stückpreis
Need More?	Angebotsanfrage

! Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

SPEZIFIKATIONEN

Produktdetails

Wedged WindowTyp:

Physikalische und mechanische Eigenschaften

22.50	Freie Apertur CA (mm):
25.00 +0.0/-0.10	Durchmesser (mm):
3.00 ±0.20	Dicke (mm):
Fine Ground	Kanten:
82	Elastizitätsmodul (GPa):
30' ±10'	Keilwinkel (arcmin):

Optische Eigenschaften

Uncoated	Beschichtung:
1.516	Brechungsindex (n _d):
N-BK7	Substrat: ☐
N/10 over 25mm Aperture	Oberflächenebenheit (P-V):
20-10	Oberflächenqualität:
350 - 2200	Wellenlängenbereich (nm):

Materialeigenschaften

7.1 (-30 to +70°C) 8.3 (+20 to +300°C)	Thermischer Ausdehnungskoeffizient CTE (10 ⁻⁶ /°C):
---	--


Konformität mit Standards





Konform	RoHS 2015:
Anzeigen	Konformitätszertifikat:
Konform	Reach 247:


PRODUKTDDETAILS

- N-BK7-Substrate mit Keilwinkel von 30 Bogenminuten
 - N/10 Oberflächenebenheit und Oberflächenqualität 20-10
 - Ideal für die Eliminierung von Etalon-Effekten
 - [Keilfenster aus Quarzglas](#) und [plane Fenster aus N-BK7](#) sind ebenfalls verfügbar
- Die TECHSPEC® Keilfenster aus N-BK7 sind in metrischen Größen verfügbar und haben einen Keilwinkel von 30 Bogenminuten. Der Keil der Fenster eliminiert Etalon-Effekte, indem verhindert wird, dass Rückreflexionen den gleichen optischen Strahlengang haben wie der transmittierte Strahl. In Laserresonatoren helfen Keilfenster bei der Vermeidung von Laserinstabilität, Modensprüngen und Leistungsspitzen durch ungewollte Reflexionen. Keilfenster aus N-BK7 werden häufig als kostengünstigere Alternative zu Keilfenstern aus Quarzglas eingesetzt, vor allem bei Anwendungen, bei denen es keine UV-Transmission gibt oder bei denen eine hohe thermische Stabilität nicht zwingend erforderlich ist (z. B. bei VIS- oder NIR-Lasern mit geringer Leistung). Keilfenster können auch als Strahl-Sampler oder Auskopplungs-Optik genutzt werden, um Laserstrahleigenschaften wie die Strahlleistung über eine gewisse Zeitspanne zu beobachten.

TECHNISCHE INFORMATIONEN




Wavelength (nm) N-BK7 with MgF₂ Coating Typical Transmission  T (%) Wavelength (nm)	Typical transmission of a 3mm thick N-BK7 window with MgF₂ (400-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$ (N-BK7) Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS-EXT Coating Typical Transmission  T (%) Wavelength (nm)	Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS-NIR Coating Typical Transmission  T (%) Wavelength (nm)	Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 880\text{nm}$ $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$ $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with VIS 0° Coating Typical Transmission  T (%) Wavelength (nm)	Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.4\% @ 425 - 675\text{nm}$ Data outside this range is not guaranteed and is for reference only. Click Here to Download Data
N-BK7 with YAG-BBAR Coating Typical Transmission  T (%)	Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{abs} \leq 0.25\% @ 532\text{nm}$ $R_{abs} \leq 0.25\% @ 1064\text{nm}$ $R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$ Data outside this range is not guaranteed and is for reference



Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with NIR I Coating
Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% \text{ @ } 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

N-BK7 with NIR II Coating
Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{abs} \leq 1.5\% \text{ @ } 750 - 800\text{nm}$$

$$R_{abs} \leq 1.0\% \text{ @ } 800 - 1550\text{nm}$$

$$R_{avg} \leq 0.7\% \text{ @ } 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)