

Bandpassfilter, 676 nm ZWL, 11,8 mm Durchm.



Produkt **#28-484** AUSVERKAUF **20+ In Stock**

-

1

+

€19^{,95}

+ WARENKORB

Mengenrabatte	
Stk. 1+	€19,95 stückpreis
Need More?	Angebotsanfrage

Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails

Bandpass Filter	Typ:
Kr Emission Line	Typische Anwendungen:

Physikalische und mechanische Eigenschaften

11.80	Durchmesser (mm):
4.60	Dicke (mm):

±0.2	Toleranz Größe (mm):
Optische Eigenschaften	
≥3.0	Optische Dichte OD:
676.00	Zentralwellenlänge ZWL (nm):
±2	Toleranz Zentralwellenlänge ZWL (nm):
10.00	Halbwertsbreite FWHM (nm):
50	Min. Transmission (%):
80-50	Oberflächenqualität:
200 - 1200	Blockungsbereich (nm):
Konformität mit Standards	
Anzeigen	Konformitätszertifikat:

Produktdetails

- Ideal for Selectively Transmitting a Narrow Range of Wavelengths
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Bandpass interference filters are used extensively in a variety of biotech, biomedical, or quantitative chemical applications to selectively transmit a narrow range of wavelengths while blocking all others. Experimental Grade Bandpass Interference Filters are available in a variety of bandpass ranges in 11.8mm and 24.15mm diameter unmounted options.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technische Informationen

