

Corning® Varioptic® Treiberboard für Flüssiglinse mit variablem Fokus mit Maxim MAX14574 Treiber und I2C/DC Eingang



Corning® Varioptic® Variable Focus Liquid Lens Driver Board with Maxim MAX14574 Driver and I2C/DC Input



Produkt #12-248 3-4 Tage

- 1 + **€250,00**

+ WARENKORB

Stk. 1+

€250,00

Mengenrabatte

[Angebotsanfrage](#)

ⓘ Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich



Größe (mm):

23 x 18 x 8

Hinweis:

This board includes a MAX 14574 Maxim driver and

various FPC connectors (4 pin and 6 pin). It has a 4 pin JST connector for DC power supply and for I²C communication. It has been designed for fast driving of the adjustable lens directly from a microcontroller, an FPGA, a DSP, etc. A cabled JST connector is supplied with the board.

When used with an A-39Nx lens, the jumper in ST2 must be removed to ensure optimal performance and product lifetime. Watch this [video](#), or view the Technical Information tab, for more information

Konformität mit Standards

RoHS 2015:
[Konform](#)

Reach 224:
[Konform](#)

Konformitätszertifikat:
[Anzeigen](#)