



NOTES:

- 1. SUBSTRATE  
UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)  
HARD COATED  
PERFORMANCE SPECS:  
T(AVG) = 90% FROM 770 - 1100nm @ 45 ° AOI  
R(AVG) = 98% FROM 450 - 744nm @ 45 ° AOI  
T(ABS) = 50% @ 757nm @ 45 ° AOI



3. FINE GRIND SURFACE

- 4. SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 5. TRANSMITTED WAVEFRONT DISTORTION RMS @ 632.8nm ≤1λ
- 6. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO		TITLE	757nm, 25.2 X 35.6mm, DICHOIC FILTER	
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	22.00 x 32.00	22.00 x 32.00				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	87066
					SHEET 1 OF 1	