





+ 0.4861
x 0.5876
■ 0.6563



SURFACE: 10A

DP1: 0.000 MM

SPOT DIAGRAM

45267
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 6.740
GD RADIUS : 18.133
SCALE BAR : 40


REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

CHROMATIC FOCAL SHIFT

45267
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 179.0264 μm
DIFFRACTION LIMITED RANGE: 21.031 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM




TRANSVERSE RAY FAN PLOT

45267
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



POLYCHROMATIC DIFFRACTION MTF

45267
TUE DEC 16 2008
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM