






49938INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 10.018
GD RADIUS : 17.952
SCALE BAR : 40

REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49938INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 96.9970 μm
DIFFRACTION LIMITED RANGE: 6.085 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

49938INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 100.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

49938INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE



POLYCHROMATIC DIFFRACTION MTF

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)