





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**




BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	700
FULL WIDTH HALF MAX (FWHM)	80nm ± 2nm
MINIMUM TRANSMISSION	60%
BLOCKING	200 - 1200
SURFACE QUALITY	80-50
COATING TYPE	TRADITIONAL COATED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE:  $\varnothing 11.8\text{mm}$ , 700nm x 80nm, BANDPASS FILTER

DWG NO: 46154

SHEET 1 OF 1