





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $\tau_{ip}(\%)$	93
PASSBAND LIMIT $\lambda_p(\text{nm})$	600
CUT-OFF POSITION $\lambda_c(\text{nm})$	530±6
STOPBAND LIMIT $\lambda_s(\text{nm})$	460
WAVELENGTH	VIS
BEVEL	PROTECTIVE AS NEEDED

Edmund Optics®



ALL DIMS IN

mm

TITLE

Ø50mm, SCHOTT OG-530 LONGPASS FILTER

DWG NO

66086

SHEET
1 OF 1