




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	550nm
TRANSMISSION WAVELENGTH	575 - 2000nm
REJECTION WAVELENGTH	415 - 515nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED



THIRD ANGLE PROJECTION		TITLE	M25.5 x 0.5, 550nm MOUNTED LONGPASS FILTER
ALL DIMS IN	mm	DWG NO	66672
			SHEET 1 OF 1