





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	488nm
FULL WIDTH HALF MAX (FWHM)	3 ± 1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	350 - 483 & 553 - 650nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

TITLE

Ø12.5mm, 488nm CWL, 3nm FWHM, HARD  
COATED LASER CLEAN-UP FILTER

DWG NO

68840

SHEET  
1 OF 1