





NOTES:

1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: Protected Aluminum (400-700nm)
R(AVG) >85% @ 400 - 700nm @ 45°
- S2: NONE
3. SEAMED EDGES
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®				
SHAPE	PLANO	PLANO	<div>THIRD ANGLE PROJECTION</div> 				
SURFACE QUALITY	80-50	N/A					
SURFACE FLATNESS	4 - 6λ	N/A					
CLEAR APERTURE	Ø 68.4 x 91.8	N/A	TITLE				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	76 x 102mm, 4-6λ Mirror	
						40041	SHEET 1 OF 1