## NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 40% R ±5% @ 550nm 60% T ±5% @ 550nm

S2: NONE

**EDGES CUT** 





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

SHEET

1 OF 1

	REV. A	\$1	\$2
	SHAPE	PLANO	PLANO
	SURFACE QUALITY	80-50	80-50
	SURFACE FLATNESS	4 - 6λ	4 - 6λ
	BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

			<b>Edmund Optic</b>	;S®
THIRD ANGLE PROJECTION	$\phi \Box$	TITLE	18 x 30mm, 40 R/60 T, PLATE BEAMSPL	ITTER
ALL DIMS IN	mm	DWG NO	46689	SHEE 1 OF