




**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



SURFACE FLATNESS	2λ
PARALLELISM (arcmin)	≤3.5
CLEAR APERTURE (%)	≥90
EDGES	Chrome, Nickel, and Gold
WAVELENGTH RANGE (nm)	200 - 5500
WAVELENGTH RANGE (μm)	0.2 - 5.5
SOLDERABILITY	MIL-STD-883
RoHS	COMPLIANT

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO<sup>®</sup> Edmund Optics<sup>®</sup>**

THIRD ANGLE PROJECTION		TITLE	10mm Diameter Uncoated, Metalized Sapphire Window		
		DWG NO	65895	SHEET 1 OF 1	