



NOTES:

- 1. SUBSTRATE:
Film
- 2. COATING (APPLY ACROSS COATING APERTURE)
TRANSMISSION : >90%
- 3. RETARDANCE: $\lambda/4$
- 4. PHASE SHIFT : 90°
- 5. HAZE: <0.2%
- 6. WAVELENGTH RANGE: 450 - 700nm
- 7. CONSTRUCTION: Polarizing Film
- 8. ROHS: COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	100 x 100mm, $\lambda/4$ Retarder Film
ALL DIMS IN	mm	DWG NO	88252
			SHEET 1 OF 1