



NOTES:

- 1. SUBSTRATE: UV FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: ALUMINUM WITH PROTECTIVE OVERCOAT
  - R(AVG) > 85% FROM 400-700nm @ 0° AOI
  - R(AVG) > 90% FROM 400-2,000nm @ 0° AOI
- S2: UV-VIS
- R(AVG) ≤ 1.5% FROM 250-700nm @ 0° AOI
- R(ABS) ≤ 1.0% FROM 350-450nm @ 0° AOI

3 FINE GRIND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div><div><div>EO<sup>®</sup></div><div>Edmund Optics<sup>®</sup></div></div></div><div><div><div>TITLE</div><div>RA FS PRISM HT 1/20 WAVE ALUM 15mm</div></div><div><div>DWG NO</div><div>39843</div></div><div><div>SHEET</div><div>1 OF 1</div></div></div></div>		
SHAPE	PLANO	PLANO			
SURFACE QUALITY	20-10	20-10			
CLEAR APERTURE	13.50 x 19.08	Ø13.50			
SURFACE FLATNESS	λ/20	λ/20			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	THIRD ANGLE PROJECTION		
			ALL DIMS IN	mm	