


NOTES:

1. COATING (APPLY ACROSS COATING APERTURE)
ULTRAFAST ENHANCED SILVER
R(AVG) > 99% @ 600 - 1000nm @ 0° AOI
Rs > 99% @ 540 - 1000nm @ 45° AOI
Rp > 98.5% @ 730 - 870nm @ 45° AOI
- DAMAGE THRESHOLD,
PULSED: 0.3 J/cm² @ 800nm, 48fs, 1 PULSE (TYPICAL)
0.16 J/cm² @ 800nm, 48fs, 100Hz, 1000 PULSES (TYPICAL)



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO
CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR
REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	Infinite Conjugate, Ultrafast Enhanced Siler, 10X/0.23NA ReflX Objective	
ALL DIMS IN	mm	DWG NO	13408	SHEET 1 OF 1