



NOTES:

1. SUBSTRATE:
N-BK7
2. S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)
S1 & S2: R(ABS) <0.25% @ 532nm
R(ABS) <0.25% @ 1064nm
R(AVG) <1.0% @ 500 - 1100nm

4. FINE GRIND SURFACE


5. RoHS COMPLIANT

6. SURFACE FLATNESS (P-V): $\lambda/4$ (per inch over clear aperture)



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION 	TITLE	50mm DIA., 6mm THICK, YAG-BBAR COATED, $\lambda/4$ N-BK7 WINDOW	
SURFACE QUALITY	60-40	60-40				
CLEAR APERTURE	$\varnothing 45.00$	$\varnothing 45.00$	ALL DIMS IN	mm	DWG NO	13328
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				SHEET 1 OF 1