





NOTES:


1. SUBSTRATE: XP42 LAMINATED BETWEEN GLASS
2. CONSTRUCTION: LAMINATED GLASS POLARIZING FILM
3.  EDGE CUT
4. EXTINCTION RATIO: 9000:1
5. OPERATING TEMPERATURE (°C): -10 TO +55
6. WAVELENGTH RANGE (nm): 425 - 700
7. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

THIRD ANGLE PROJECTION 		TITLE	20mm Dia., VIS Coated, Linear Glass Polarizer (XP42)	
ALL DIMS IN	mm	DWG NO	19649	SHEET 1 OF 1