




NOTES:  
1. SUBSTRATE:  
BOROFLOAT®

3. COATING  
S1: Enhanced Aluminum (450-650nm)  
R(AVG) >95% @ 450 - 650nm

S2:NONE  
3. FINE GRIND SURFACE


4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60 - 40	COMMERCIAL POLISH
CLEAR APERTURE	31.50 x 45.00	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	35 x 50mm Enhanced Aluminum, λ/4 Mirror
ALL DIMS IN	mm	DWG NO	25750
			SHEET 5 OF 8