


Protected Silver (Second Surface) Coating Curve

Coating Specification @ 45°: $R_{\text{abs}} > 87\%$ @ 450 - 500nm, $R_{\text{abs}} > 94\%$ @ 500 - 2000nm, $R_{\text{avg}} > 96\%$ @ 400 - 2500nm

Note: Due to material absorption of N-BK7, reduced reflectivity is observed beyond 2000nm.



© COPYRIGHT 2020 EDMUND OPTICS, INC. ALL RIGHTS RESERVED