



NOTES:

- 1. COATING:  
S1: SPECTRAL BLACK™  
THICKNESS: 3 - 7 (µm)
- 2. ABSORBANCE: 99.5 - 99.7 (0 - 10° AOI) %
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -40 TO +150
- 6. WAVELENGTH RANGE (µm): 0.3 - 14




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



THIRD ANGLE PROJECTION 		TITLE	10 x 10cm Sheet of Spectral Black Foil, Low Outgassing Adhesive	
ALL DIMS IN	mm	DWG NO	28942	SHEET 1 OF 1