


TECHSPEC®

Plankonvexe Linse, 12,7 mm D. x 30,0 mm BW, VIS-EXT-beschichtet



Produkt **#38-463** **2 In Stock**

[Andere Beschichtungen](#)

-

1

+

€49<sup>.00</sup>

+ WARENKORB

| Mengenrabatte |                                 |
|---------------|---------------------------------|
| Stk. 1-9      | €49,00 stückpreis               |
| Stk. 10-24    | €44,00 stückpreis               |
| Stk. 25-49    | €39,25 stückpreis               |
| Need More?    | <a href="#">Angebotsanfrage</a> |

!

 Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

Produktdetails

Plano-Convex Lens

Typ:

Physikalische und mechanische Eigenschaften

|                      |                             |
|----------------------|-----------------------------|
| 12.70 +0.0/-0.025    | Durchmesser (mm):           |
| <1                   | Zentrierung (Bogenminuten): |
| 2.70 ±0.10           | Mittendicke CT (mm):        |
| 1.34                 | Randdicke ET (mm):          |
| 11.7                 | Freie Apertur CA (mm):      |
| Protective as needed | Fase:                       |

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| Optische Eigenschaften               |                                                        |
| 30.00 @ 587.6nm                      | Effektive Brennweite EFL (mm):                         |
| 28.22                                | Hintere Brennweite BFL (mm):                           |
| VIS-EXT (350-700nm)                  | Beschichtung:                                          |
| R <sub>avg</sub> <0.5% @ 350 - 700nm | Beschichtungsspezifikation:                            |
| N-BK7                                | Substrat: <input type="checkbox"/>                     |
| 40-20                                | Oberflächenqualität:                                   |
| 1.5λ                                 | Power (P-V) @ 632,8 nm:                                |
| λ/4                                  | Unregelmäßigkeit (P-V) @ 632,8 nm:                     |
| ±1                                   | Toleranz Brennweite (%):                               |
| 15.51                                | Radius R <sub>1</sub> (mm):                            |
| 2.36                                 | Blende:                                                |
| 0.21                                 | Numerische Apertur NA:                                 |
| 350 - 700                            | Wellenlängenbereich (nm):                              |
| 5 J/cm <sup>2</sup> @ 532nm, 10ns    | Zerstörschwelle, laut Design: <input type="checkbox"/> |


|                           |                         |
|---------------------------|-------------------------|
| Konformität mit Standards |                         |
| Konform                   | RoHS 2015:              |
| Anzeigen                  | Konformitätszertifikat: |
| Konform                   | Reach 235:              |






## Produktdetails





- Breitband-Antireflexbeschichtung für das sichtbare Spektrum mit verbesserten UV-Eigenschaften
- Reflexion pro Oberfläche <0,5% im Bereich von 350 – 700 nm
- Für 0° Einfallswinkel ausgelegt
- Verschiedene Beschichtungen erhältlich: [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#) und [YAG-BBAR](#) oder [unbeschichtet](#)

TECHSPEC® Plankonvexe Linsen (PCX) mit VIS-EXT-Beschichtung haben eine positive Brennweite und sind ideal für die Fokussierung von Licht in abbildenden Anwendungen. Sie können gut in Verbindung mit Emittern, Detektoren, Lasern und Faseroptiken eingesetzt werden. TECHSPEC® Plankonvexe Linsen (PCX) mit VIS-EXT-Beschichtung sind in einer Vielzahl von Durchmessern und Brennweiten erhältlich. Identische Designs dieser Linsen werden auch [unbeschichtet](#) oder mit breitbandigen Antireflexionsbeschichtungen (BBAR) angeboten, dazu gehören [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#) und [YAG-BBAR](#).

## Technische Informationen



|                                                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| N-BK7                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| <div data-bbox="262 216 1249 736"><h3>Uncoated N-BK7 Typical Transmission</h3></div>                       | <div data-bbox="1339 424 1843 513"><p>Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV - NIR spectra.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                                                                                                                                                                                                                                                                                                        |
| <div data-bbox="262 810 1213 1291"><h3>N-BK7 with MgF<sub>2</sub> Coating Typical Transmission</h3></div> | <div data-bbox="1339 899 1843 1151"><p>Typical transmission of a 3mm thick N-BK7 window with MgF2 (400-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 1.75\% \text{ @ } 400 - 700\text{nm (N-BK7)}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                               |
| <div data-bbox="262 1329 1249 1914"><h3>N-BK7 with VIS-EXT Coating Typical Transmission</h3></div>       | <div data-bbox="1339 1492 1843 1745"><p>Typical transmission of a 3mm thick N-BK7 window with VIS-EXT (350-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                                    |
| <div data-bbox="262 1973 1234 2537"><h3>N-BK7 with VIS-NIR Coating Typical Transmission</h3></div>       | <div data-bbox="1339 2086 1843 2412"><p>Typical transmission of a 3mm thick N-BK7 window with VIS-NIR (400-1000nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><br/><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><br/><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |
| <div data-bbox="262 2591 1171 2887"><h3>N-BK7 with VIS 0° Coating Typical Transmission</h3></div>        | <div data-bbox="1339 2724 1843 2902"><p>Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 0.4\% \text{ @ } 425 - 675\text{nm}</math></p><p>Data outside this range is not guaranteed and is for reference only.</p></div>                                                                                                                                                                                       |

|                                                                                                                                                              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                             | <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                                                                                                                                                                                                                                                                                                      |
| <p><b>N-BK7 with YAG-BBAR Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 0.25\% @ 532\text{nm}</math><br/><math>R_{abs} \leq 0.25\% @ 1064\text{nm}</math><br/><math>R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>           |
| <p><b>N-BK7 with NIR I Coating</b><br/><b>Typical Transmission</b></p>   | <p>Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p>                                                                                                                     |
| <p><b>N-BK7 with NIR II Coating</b><br/><b>Typical Transmission</b></p>  | <p>Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.</p> <p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <p><math>R_{abs} \leq 1.5\% @ 750 - 800\text{nm}</math><br/><math>R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}</math><br/><math>R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}</math></p> <p>Data outside this range is not guaranteed and is for reference only.</p> <p><a href="#">Click Here to Download Data</a></p> |

## Kundenspezifische Produkte

Edmund Optics bietet einen umfangreichen kundenspezifischen Fertigungsservice für Optik- und Bildverarbeitungskomponenten an, speziell hergestellt für Ihre Anwendungsanforderungen. Wir ermöglichen flexible Lösungen für Ihre Bedürfnisse – von der Prototypenphase bis zur Serienfertigung. Unsere erfahrenen IngenieurInnen freuen sich auf die Zusammenarbeit und unterstützen Sie bei jedem Projektschritt.

Unser Service beinhaltet:

- Kundenspezifische Abmessungen, Materialien und mehr
- Hochpräzise Oberflächenqualität und -ebenheit
- Enge Toleranzen und komplexe Formen
- Skalierbare Produktion – vom Prototypen zur Serie

Erfahren Sie mehr über unsere [kundenspezifischen Fertigungsmöglichkeiten](#) oder senden Sie [hier](#) eine Anfrage.

## Kompatible Halterungen

