

TECHSPEC<sup>®</sup> 1λ-Quarzglasfenster, 50,8 mm Durchmesser, 1 mm Dicke, UV-VIS-beschichtet



TECHSPEC<sup>®</sup> 1λ UV Fused Silica Windows

Produkt **#25-269** **1 In Stock**

-

1

+

€175<sup>00</sup>

+ WARENKORB

| Mengenrabatte |                                 |
|---------------|---------------------------------|
| Stk. 1-5      | €175,00 stückpreis              |
| Stk. 6-25     | €139,00 stückpreis              |
| Stk. 26-49    | €131,00 stückpreis              |
| Need More?    | <a href="#">Angebotsanfrage</a> |

Preise exklusiv der geltenden Mehrwertsteuer und Abgaben

Downloadbereich

313.00

#Sorting:

Produktdetails

Protective Window

Typ:

Physikalische und mechanische Eigenschaften

Freie Apertur CA (mm):

|                              |                      |
|------------------------------|----------------------|
| 45.72                        |                      |
| Durchmesser (mm):            | 50.80 +0.00/-0.20    |
| Dicke (mm):                  | 1.00 ±0.38           |
| Parallelität (Bogenminuten): | <5                   |
| Fase:                        | Protective as needed |
| Freie Apertur (%):           | 90                   |
| Kanten:                      | Fine Ground          |
| Poisson-Zahl:                | 0.16                 |
| Elastizitätsmodul (GPa):     | 73                   |
| Knoop-Härte (kg/mm²):        | 522.00               |

| Optische Eigenschaften            |                                                                              |
|-----------------------------------|------------------------------------------------------------------------------|
| Beschichtung:                     | UV-VIS (250-700nm)                                                           |
| Substrat: <div></div>             | <a href="#">Fused Silica</a> (Corning 7980)                                  |
| Brechungsindex (n <sub>d</sub> ): | 1.458                                                                        |
| Oberflächenqualität:              | 60-40                                                                        |
| Transmittierte Wellenfront, P-V:  | 1λ                                                                           |
| Abbe-Zahl (v <sub>d</sub> ):      | 67.8                                                                         |
| Beschichtungsspezifikation:       | R <sub>abs</sub> ≤1.0% @ 350 - 450nm<br>R <sub>avg</sub> ≤1.5% @ 250 - 700nm |
| Wellenlängenbereich (nm):         | 250 - 700                                                                    |
| Zerstörschwelle, Referenz:        | 3 J/cm² @ 355nm, 10ns<br>5 J/cm² @ 532nm, 10ns                               |

| Materialeigenschaften                                          |                                                                   |
|----------------------------------------------------------------|-------------------------------------------------------------------|
| Dichte (g/cm³):                                                | 2.20                                                              |
| Thermischer Ausdehnungskoeffizient CTE (10 <sup>-6</sup> /°C): | 0.52 (+5 to +35°C)<br>0.57 (0 to +200°C)<br>0.48 (-100 to +200°C) |

| Konformität mit Standards |                          |
|---------------------------|--------------------------|
| RoHS 2015:                | <a href="#">Konform</a>  |
| Konformitätszertifikat:   | <a href="#">Anzeigen</a> |
| Reach 235:                | <a href="#">Konform</a>  |

## Produktdetails

- Lieferbar ohne Beschichtung oder mit breitbandiger Antireflexionsbeschichtung
- Ideal für kostenkritische breitbandige Anwendungen
- Rund oder quadratisch mit Größen von 5 mm bis 100 mm
- [λ/4](#)- oder [λ/10](#)-Fenster aus UV-Quarzglas ebenfalls erhältlich

TECHSPEC® 1λ-Fenster aus UV-Quarzglas werden präzise aus synthetischem UV-Quarzglas gefertigt. Das synthetische Quarzglas hat nicht nur bessere Transmissionseigenschaften, sondern auch bessere thermische Eigenschaften und zeichnet sich durch außergewöhnliche Reinheit und Beständigkeit gegenüber Umwelteinflüssen bei anspruchsvollen Anwendungen aus. Die Fenster eignen sich ideal für kostensensible Breitband-Anwendungen und sind sowohl unbeschichtet als auch mit breitbandiger Antireflexionsbeschichtung lieferbar. TECHSPEC® 1λ-Fenster aus UV-Quarzglas werden rund oder quadratisch mit Größen von 5 mm bis 100 mm angeboten.

**Bitte beachten Sie:** Neue Produkte, die zu dieser Produktfamilie hinzugefügt werden, können mit der transmittierten Wellenfrontverzerrung (TWD) und nicht mehr mit der Oberflächenebenheit spezifiziert sein. Weitere Informationen über den Unterschied zwischen den beiden Spezifikationen finden Sie unter [Grundlagen optischer Fenster](#).

## Technische Informationen



UV FS Transmission Curve



| FUSED SILICA                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |  |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|
| <div><h3>Uncoated Fused Silica<br/>Typical Transmission</h3><p>Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.</p><p><a href="#">Click Here to Download Data</a></p></div>                                                                                                                                                                                                                                                                                               |  |  |
| <div><h3>Fused Silica with MgF<sub>2</sub> Coating<br/>Typical Transmission</h3><p>Typical transmission of a 3mm thick fused silica window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.</p><p>The blue shaded region indicates the coating design wavelength range, with the following specification:</p><p><math>R_{avg} \leq 1.75\% @ 400 - 700\text{nm}</math> (N-BK7)</p><p>Data outside this range is not guaranteed and is for reference only.</p><p><a href="#">Click Here to Download Data</a></p></div> |  |  |

|                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <p data-bbox="583 261 1075 371"><b>Fused Silica with UV-AR Coating</b><br/><b>Typical Transmission</b></p>        | <p data-bbox="1329 424 1854 474">Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.</p> <p data-bbox="1329 486 1854 537">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 549 1707 626"><math>R_{abs} \leq 1.0\% \text{ @ } 250 - 425\text{nm}</math><math>R_{avg} \leq 0.75\% \text{ @ } 250 - 425\text{nm}</math><math>R_{avg} \leq 0.5\% \text{ @ } 370 - 420\text{nm}</math></div> <p data-bbox="1329 638 1854 688">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 700 1707 721"><a href="#">Click Here to Download Data</a></p>           |
| <p data-bbox="575 943 1083 1053"><b>Fused Silica with UV-VIS Coating</b><br/><b>Typical Transmission</b></p>    | <p data-bbox="1329 1101 1854 1151">Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1163 1854 1213">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 1225 1707 1279"><math>R_{abs} \leq 1.0\% \text{ @ } 350 - 450\text{nm}</math><math>R_{avg} \leq 1.5\% \text{ @ } 250 - 700\text{nm}</math></div> <p data-bbox="1329 1314 1854 1365">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 1377 1707 1397"><a href="#">Click Here to Download Data</a></p>                                                              |
| <p data-bbox="569 1626 1087 1736"><b>Fused Silica with VIS-EXT Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 1804 1854 1855">Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.</p> <p data-bbox="1329 1866 1854 1917">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 1929 1707 1955"><math>R_{avg} \leq 0.5\% \text{ @ } 350 - 700\text{nm}</math></div> <p data-bbox="1329 1967 1854 2018">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 2030 1707 2050"><a href="#">Click Here to Download Data</a></p>                                                                                                                          |
| <p data-bbox="575 2309 1083 2418"><b>Fused Silica with VIS-NIR Coating</b><br/><b>Typical Transmission</b></p>  | <p data-bbox="1329 2442 1854 2493">Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.</p> <p data-bbox="1329 2504 1854 2555">The blue shaded region indicates the coating design wavelength range, with the following specification:</p> <div data-bbox="1476 2567 1707 2644"><math>R_{abs} \leq 0.25\% \text{ @ } 880\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 400 - 870\text{nm}</math><math>R_{avg} \leq 1.25\% \text{ @ } 890 - 1000\text{nm}</math></div> <p data-bbox="1329 2674 1854 2724">Data outside this range is not guaranteed and is for reference only.</p> <p data-bbox="1476 2736 1707 2757"><a href="#">Click Here to Download Data</a></p> |



Typical transmission of a 3mm thick fused silica window with MS  
0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

Typical transmission of a 3mm thick fused silica window with  
YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{abs}} \leq 0.25\% @ 532\text{nm}$$

$$R_{\text{abs}} \leq 0.25\% @ 1064\text{nm}$$

$$R_{avg} \leq 1.0\% @ 500 - 1100\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick fused silica window with NIR  
I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick fused silica window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{abs}} \leq 1.5\% @ 750 - 800\text{nm}$

$$R_{\text{abs}} \leq 1.0\% @ 800 - 1550\text{nm}$$

$$R_{\text{avg}} \leq 0.7\% @ 750 - 1550\text{nm}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

# Kundenspezifische Produkte

Edmund Optics bietet einen umfangreichen kundenspezifischen Fertigungsservice für Optik- und Bildverarbeitungskomponenten an, speziell hergestellt für Ihre Anwendungsanforderungen. Wir ermöglichen flexible Lösungen für Ihre Bedürfnisse – von der Prototypenphase bis zur Serienfertigung. Unsere erfahrenen IngenieurInnen freuen sich auf die Zusammenarbeit und unterstützen Sie bei jedem Projektschritt.

Unser Service beinhaltet:

- Kundenspezifische Abmessungen, Materialien und mehr
- Hochpräzise Oberflächenqualität und -ebenheit
- Enge Toleranzen und komplexe Formen
- Skalierbare Produktion – vom Prototypen zur Serie

Erfahren Sie mehr über unsere [kundenspezifischen Fertigungsmöglichkeiten](#) oder senden Sie [hier](#) eine Anfrage.